


# Emerson Quick Ship for Appleton™ LED Lighting Products Within the United States




Our Quick Ship Program is a world-class fulfillment program that allows for fast shipment of select Appleton LED products to maximize speed and responsiveness. It leverages our local infrastructure, local presence, and our commitment to service to help you avoid downtime, stay on schedule, respond to the unexpected, and control costs in today's challenging environments.

Put Emerson's wealth of resources and expertise to work for you with our made-to-stock products – shipped within 5 days of order receipt to continental US locations<sup>Ⓞ</sup>. Contact us about your specific requirements at 800-621-1506 or locate a representative in your area at [www.masteringled.com](http://www.masteringled.com).


## Areamaster™ Generation 2 Series | Low Lumen

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	9000	5000K	Clear Glass	NEMA 7x7	120-277 Vac, 50/60 Hz, 125-300 Vdc	AMLGL6CG6BU	5
	15000	5000K	Clear Glass	NEMA 7x6		AMLGL7CG7BU	5
	15000	5000K	Clear Glass	NEMA 7x7		AMLGL7CG6BU	10
	15000	5000K	Clear Glass	NEMA 7x6	347-480 Vac, 50/60 Hz	AMLGL7CG7BH	5
	15000	5000K	Clear Glass	NEMA 7x7		AMLGL7CG6BH	5
	19000	5000K	Clear Glass	NEMA 7x6		AMLGL8CG7BU	5
	19000	5000K	Clear Glass	NEMA 7x7	120-277 Vac, 50/60 Hz, 125-300 Vdc	AMLGL8CG6BU	5
	19000	5000K	Clear Glass	NEMA 7x7	347-480 Vac, 50/60 Hz	AMLGL8CG6BH	5





## Areamaster Generation 2 Series | High Lumen

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	24000	5000K	Clear Glass	NEMA 7x7	120-277 Vac, 50/60 Hz, 125-300 Vdc	AMLHL1CG6BU	5
	24000	5000K	Clear Glass	NEMA 7x7	347-480 Vac, 50/60 Hz	AMLHL1CG6BH	10

## Industrial Areamaster Generation 2 Series | Low Lumen

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	15000	5000K	Clear Glass	NEMA 7x6	120-277 Vac, 50/60 Hz, 125-300 Vdc	IAMLGL7CG7BU	10
	15000	5000K	Clear Glass	NEMA 7x7		IAMLGL7CG6BU	5
	19000	5000K	Clear Glass	NEMA 7x6	120-277 Vac, 50/60 Hz, 125-300 Vdc	IAMLGL8CG7BU	10


## Areamaster Accessories

	Description	Catalog Number	Max. Qty.
	Pipe or Wall Mount Bracket   Used with GAM8CA   Clamps to 1" to 2-1/2" pipe	GAM8WB	5
	Poletop Slip-Fitter   Slip-fits 1-1/2" or 2" pipe size poletop tenons	GSF20	10
	Poletop Slip-Fitter   Slip-fits 2" or 2-1/2" pipe size poletop tenons	GAM8SF	10
	Safety Cable   Stainless steel	LEDSC	10


## Rigmaster™ LED Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	8000	5000K	Clear Polycarbonate Lens	4 ft   Linear	120-277 Vac, 50/60 Hz; 125-300 Vdc	RMA42CPLBUNGW2	15

## Explosionproof Rigmaster LED Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	4000	5000K	Clear Glass Lens	2 ft   Linear	120-277 Vac, 50/60 Hz; 125-300 Vdc	ERMB22CCLBUNGW	5
	8000	5000K	Clear Glass Lens	4 ft   Linear		ERMB42CCLBUNGW	10

## Rigmaster Accessories


	Description	Catalog Number	Max. Qty.
	Safety Cable   Stainless steel	LEDSC	10

Ⓞ Order must be received before 12:00 pm CT. Maximum order quantities apply. Transit times will vary based upon distance.


# Emerson Quick Ship for Appleton™ LED Lighting Products Within the United States




## Mercmaster™ LED Generation 3 Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	9,500	5000K	Clear Polycarbonate Globe	Type V	120-277 Vac, 50/60 Hz; 125-300 Vdc	MLGL9CP5BU	5
	9,500	5000K	Diffused Polycarbonate Globe	Type V		MLGL9CD5BU	10

## Mercmaster LED Low Profile Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	4000	5000K	Clear Polycarbonate Globe	Type V	120-277 Vac, 50/60 Hz; 125-300 Vdc	MLLED3CP5BU	10
	5000	5000K	Diffused Polycarbonate Globe	Type V		MLLED4CD5BU	15
	5000	5000K	Diffused Polycarbonate Globe	Type V	347-480 Vac, 50/60 Hz	MLLED4CD5BH	10









## Contender™ LED Series †

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	5000	5000K	Diffused Polycarbonate Globe	Type V	120-277 Vac, 50/60 Hz; 125-300 Vdc	VMV5LCD5BU	15
	4000	5000K	Diffused Polycarbonate Globe	Type V		VMV4LCD5BU	5

## Industrial Mercmaster LED Low Profile Series

	Lumens	CCT	Globe Material/Diffusion	Light Distribution	Voltage	Catalog Number	Max. Qty.
	5000	5000K	Diffused Polycarbonate Globe	Type V	120-277 Vac, 50/60 Hz; 125-300 Vdc	IMLLED4CD5BU	10

## Mercmaster Accessories

	Description	Catalog Number	Max. Qty.
	Mounting Hood   Pendant   One Hub, Rigid Mounting   3/4" NPT	KPA75	20
	Mounting Hood   Ceiling   Five Hubs, Four Close-Up Plugs   3/4" NPT	KPC75	20
	Mounting Hood   Wall   Five Hubs, Four Close-Up Plugs   3/4" NPT	KPWB75	20
	Mounting Hood   25° Stanchion   One Hub   1-1/2" NPT	KPS150	20
	Mounting Hood   25° Stanchion   One Hub   1-1/4" NPT	KPS125	10
	Mounting Hood   90° Stanchion   One Hub   1-1/2" NPT	KPST150	10
	Mounting Hood Adapter   Crouse-Hinds™ Champ® †   Pendant, Flexible Pendant, Ceiling	MMADCHVS	10
	Mounting Hood Adapter   Crouse-Hinds™ Champ® †   Wall, 25° and 90° Angle Stanchion	MMADCHVA	10
	Visor   Dark Sky Compliant	MMVISOR	10

## Mercmaster and Contender Accessories

	Description	Catalog Number	Max. Qty.
	Globe Guard   Stainless steel wire	MGU1	15
	Safety Cable   Stainless steel	LEDSC	10

Ⓢ Order must be received before 12:00 pm CT. Maximum order quantities apply. Transit times will vary based upon distance.

† Mounts directly to the following Crouse Hinds™ Champ® VMV mounting hoods. | Crouse-Hinds is a registered trademark of Cooper Industries, Inc.